Technical Data Sheet

Bondloc BCA LV Superglue Revised 03.08.10



Bondloc BCA LV Superglue

APPLICATIONS

BCA LV Superglue bonds metals, plastics, wood, ceramics, rubber, leather, card, glass and many other materials.

INSTRUCTIONS FOR USE

Clean and dry surfaces to be bonded. Apply adhesive sparingly to one surface and assemble parts. Hold or clamp parts together for 60 seconds. Leave for 1 hour to fully cure. Activators and primers may be used to aid bonding.

LIQUID PROPERTIES

Ester base	Ethyl cyanoacrylate
Appearance	Clear, colourless
Specific Gravity 25°C	1.06 g/cm2
Shelf life	12 months unopened
Viscosity @ 25°C	25 - 35 mPas

CURED PERFORMANCE

Cured speed – defined as the time taken to develop a strength of 0.1N/mm² at 22°C and 50% relative humidity.

	ı
Balsa	<2 seconds
Nitrile	<4 seconds
Neoprene	<5 seconds
EPDM	<5 seconds
Steel	25-40 seconds
Polycarbonate	10-30 seconds
ABS	10-15 seconds

SHEAR STRENGTH

Steel	15-25 N/mm²
Aluminium	7-10 N/mm²
Nitrile Rubber	5-10 N/mm²
Polycarbonate	5-10 N/mm²
ABS	6-10 N/mm²

TENSILE STRENGTH


Nitrile Rubber	5-15 N/mm²
Neoprene	5-15 N/mm²
EPDM	2-6 N/mm²

TEMPERATURE RESISTANCE

Tested on mild steel cured for 24 hours, conditioned to test temperature for 1 hour before pull-test.

ENVIRO-CHEMICAL RESISTANCE

Exposed to conditions for 1000 hours at 22°C except for 98% RH which had an exposure of 42°C.



STORAGE

BCA LV should ideally be stored in original sealed containers until used. Containers should be stored between 2°C and 10°C with a maximum storage temperature of 25°C. Avoid exposure to strong light and heat sources. Refrigeration can prolong shelf life.

HEALTH & SAFETY

This technical information sheet does not constitute a Material Safety Data Sheet (MSDS). Before using this product ensure you have read and fully understood BCA LV MSDS.

PRESENTATION

Bottles......10g, 20g, 50g, 500g